



**YGA292N Comp Ground Lug, 250 kcmil Cu,
2-Hole NEMA Pad**

By Burndy

Catalog # [YGA292N](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Application

For Grounding Applications And Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	• UL 467,486A • CSA Certified • Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor


Conductor - Copper Str Size	250 kcmil
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	250 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.09 in
Package Height	0.000 in



Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	132 mm
Dimension - Outside Diameter inch	0.75 in
Dimension - Width fraction	1/2 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	1/2
Dimension - Stud Size fraction	1/2
Dimension - Bolt Hole Size inch	0.52 in
Dimension - B Length fraction	1-4/7 in
Dimension - Width inch	0.53 in
Dimension - B Length inch	1.57 in
Dimension - N inch	0.62 in
Dimension - Bolt Size inch	0.50 in
Dimension - Length Overall inch	5.21 in

General

Product Family	Grounding and Bonding Connectors>"Hyground" Compression Grounding Connectors>Terminals
Trade Name	HYLUG™
Die Index	16
Plated	No
Color Code	Yellow
Sub Brand	HYLUG
Product Type	Compression
UPC	781810220337
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220337
UPC 14 Digit GTIN	00781810220337

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4640
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)