



YGHA362N Comp Ground Lug, 600 kcmil Cu, 2-Hole NEMA Pad

By Burndy
Catalog # [YGHA362N](#)



HYLUG™ Copper Compression Terminal for Grounding; Heavy
Duty; 2-Hole

Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	IEEE 837
Met	
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct	No
Burial	
Industry Standard(s)	IEEE 837
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size	600 kcmil
Range	
Conductor - Copper Str Size	600 kcmil

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	2.10 in
----------------------------	---------

Package Height	0.000 in
Physical Attribute - Tongue	Straight
Angle	
Dimension - B Length fraction	1-19/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.62 in
Dimension - L Length Overall	139 mm
mm	
Dimension - B Length inch	1.38 in
Dimension - Outside Diameter	1.55 in
inch	
Dimension - D inch	3.00 in
Dimension - N inch	0.63 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall	5.48 in
inch	

General

Plated	N
Trade Name	HYLUG™
Die Index	576
UPC	781810340356
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810340356
UPC 14 Digit GTIN	00781810340356

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1044
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)