



YG14B2TC2C2C Compression Bus Bar Connector

By Burndy
Catalog # YG14B2TC2C2C

Copper Compression Bus Bar Connector, #2 AWG SOL and/or #2 AWG SOL/STR to 1/4 " Copper Busbar

Features

- Compression Busbar Connector
- Easier to use than Exothermic Connections
- Ideally suited for cellular tower applications.

Application

For Direct Barial And Cellular Tower Applicatons And Is Easier To Use Than Exothermic Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • UL 486A • CSA C22.2 No 65
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct	Yes
Burial	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size A	2 AWG
Range	
Conductor - Copper Solid Size A	2 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - Copper Solid Size A	2 AWG
Range	
Conductor - Copper Solid Size B	2 AWG
Range	
Conductor Type	• CU C Str-Size • CU C Solid-Size

- Bar-Size

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Bus Bar Size Tap Side	1/4" Thick Busbar
inch	

General

Trade Name	HYGROUND®
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYGROUND
Product Type	Compression
UPC	781810232712
Type	YG-B
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810232712
UPC 14 Digit GTIN	00781810232712

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)