




YGHP29C2MX Figure 6 Compression Grounding Connector

By Burndy
Catalog # [YGHP29C2MX](#)



COMP-SPLICE-W/O BAG-PENA

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	• 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil
Conductor - Copper Str Size B	• 5 AWG • 4 AWG • 3 AWG • 2 AWG
Conductor - Copper Str Size A Range	1/0 -250 kcmil
Conductor - Copper Str Size B Range	5 AWG-2 AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Dimension - Pad Width inch	0.43 in
Package Height	0.000 in
Dimension - B Length fraction	1/3 in
Package Weight	0.000 lb.
Dimension - Width inch	0.75 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.33 in
Dimension - D inch	0.43 in
Dimension - Width fraction	3/4 in
Dimension - Length Overall	2.09 in

General

Plated	N
Die Index	997
UPC	781810308707
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810308707
UPC 14 Digit GTIN	00781810308707

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand