



YGHA312NTNNP Comp Ground Lug, 350 kcmil Cu, 2-Hole NEMA, Tin

By Burndy
Catalog # [YGHA312NTNNP](#)

Tin plated Heavy Duty Irreversible Compression Terminals without oxide inhibitor



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed

Specifications

Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837

Conductor

Conductor Type	• CU C Str-Size • CU C Solid-Size
Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	1.62 in
Package Height	0.000 in
Physical Attribute - Tongue Angle	Straight

Dimension - Height inch	1.04 in
Dimension - Height fraction	1-1/25 in
Dimension - B Length fraction	1-9/50 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.66 in
Dimension - L Length Overall mm	126 mm
Dimension - B Length inch	1.18 in
Dimension - Outside Diameter inch	1.17 in
Dimension - D inch	3.03 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	4.96 in

General

Plated	Y
Trade Name	HYLUG™
Die Index	20
UPC	781810360606
Type	Terminals
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810360606
UPC 14 Digit GTIN	00781810360606

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2220
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)