



YGHS28TN Compression Grounding Splice, 4/0 AWG Cu, Tin Plate

By Burndy
Catalog # [YGHS28TN](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
--	---

Connector Type	Terminal
Dimensions	
Package Height	0.000 in
Dimension - B Length fraction	1-1/6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	66 mm
Dimension - B Length inch	1.18 in
Dimension - Outside Diameter inch	0.89 in
Dimension - Length Overall inch	2.59 in
General	
Plated	Y
Trade Name	HYLINK™
Die Index	17
UPC	781810110737
Type	Splices
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810110737
UPC 14 Digit GTIN	00781810110737

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3840
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)