



YGHP34C34TN Fig. 6 Cu Wire/Rod/Rebar Run to Cu Wire Tap, Tin

By Burndy
Catalog # [YGHP34C34TN](#)



Copper Compression Ground Rod Connector; 250-500 kcmil, 5/8"-3/4" Rod, 5/8"-3/4" Rebar Run, 350-500 kcmil Tap, Tin Plated

Features

- Irreversible compression ground tap can be used as a tap connector or as a tap splice connector
- UL467 Listed
- Acceptable for direct burial in earth and concrete
- Prefilled with PENETROX™ compound and strip sealed

- 450 kcmil
- 500 kcmil

Specifications

Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	Direct Burial
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Rebar Run Range	5 kcmil-6 kcmil
Conductor - Rebar Run	• 5 • 6
Conductor - Rod Run Range	5/8 in-3/4 in
Conductor - Rod Run	• 5/8 in • 3/4 in
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil
Conductor - Copper Str Tap Range	350 kcmil-500 kcmil
Conductor - Copper Str Tap	• 350 kcmil • 400 kcmil

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Tap

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	Y
Trade Name	HYTAP™
Die Index	1011
Oxide Inhibitor Type	Penetrox E
UPC	781810527290
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810527290
UPC 14 Digit GTIN	00781810527290

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5920
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)