




YGHS31 Compression Grounding Splice, 350 kcmil Cu

By Burndy
Catalog # [YGHS31](#)



HYGROUND® Grounding Irreversible Compression Splice

Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B • IEEE 837
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Splice

Dimensions

Dimension - B Length fraction	1-1/6 in
Dimension - L Length Overall	66 mm
Dimension - B Length inch	1.18 in
Dimension - Outside Diameter	1.17 in
Dimension - Length Overall	2.59 in

General

Plated	N
Trade Name	HYLINK™
Die Index	20
UPC	781810165614
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810165614
UPC 14 Digit GTIN	00781810165614

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)