




YGIBS284622N Structural Steel Compression Grounding Connector

By Burndy
Catalog # [YGIBS284622N](#)

Copper Compression Connector, Cable to Steel, 2 AWG - 4/0 AWG, Angled Flange, 0.400" - 0.462" Thickness, 2 holes, 1/2" Stud



Features

- Irreversible compression ground connector allowing attachment to a structural steel standard (Angled) or wide flange (Parallel) beam
- Made of high conductivity wrought copper and prefilled with PENETROX™ E compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	2 AWG-4/0 AWG
Conductor - Copper Str Size	2 AWG 1 AWG 1/0 2/0 AWG 3/0 AWG 4/0 AWG

Configuration

Connector Type	Tap
----------------	-----

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	3 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	76 mm
Dimension - B Length inch	3.00 in
Dimension - I Beam Thickness inch	0.400" - 0.462"
Dimension - I Beam Thickness Range inch	0.376 0.400 0.425 0.437
Dimension - Length Overall inch	3.00 in

General

Plated	N
Trade Name	GROUNDLINK™
I Beam Style	Standard Beam (Flange Angled)
UPC	781810039304
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810039304
UPC 14 Digit GTIN	00781810039304

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1782
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)