



YH4429, Compression H-Tap

By Burndy
Catalog # [YH4429](#)

Copper Compression H Tap, 1000 KCMIL-750 KCMIL (Main), 250 KCMIL-2 AWG (Tap), Tin Plated

Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application


Wire Tap

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	2 AWG-4/0 AWG
Conductor - Copper Flex K Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Flex M Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex M Run	• 500 kcmil • 600 kcmil • 700 kcmil



Conductor - Copper Flex I Tap Range	4/0 AWG-2 AWG
Conductor - Copper Flex I Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Flex K Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex K Run	• 500 kcmil • 600 kcmil • 700 kcmil
Conductor - Copper Flex G Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex G Run	• 500 kcmil • 600 kcmil • 700 kcmil
Conductor - Copper Flex H Run Range	4/0 AWG-700 kcmil
Conductor - Copper Flex H Run	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 600 kcmil • 700 kcmil
Conductor - Copper Str Run Range	1000 KCMIL-750 KCMIL
Conductor - Copper Flex G Tap Range	2 AWG-4/0 AWG
Conductor - Copper Str Run	• 700 kcmil • 750 kcmil • 800 kcmil • 850 kcmil • 900 kcmil • 1000 kcmil
Conductor - Copper Flex G Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Flex M Tap Range	2 AWG-4/0 AWG

Conductor - Copper Flex M Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Flex H Tap Range	2 AWG-4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG
Conductor - Copper Flex I Run Range	500 kcmil-700 kcmil
Conductor - Copper Flex I Run	750 KCMIL-500 KCMIL
Conductor - Copper Str Tap Range	250 KCMIL-2 AWG
Conductor - Copper Str Tap	• 2 AWG • 1 AWG • 1/0 • 2/0 AWG • 3/0 AWG • 4/0 AWG • 250 kcmil

Configuration

Connector Type	H-TAP
----------------	-------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - Height inch	3.22 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	25 mm
Dimension - Width fraction	1.70 in
Dimension - Strip Length inch	1-3/8
Dimension - Width inch	3.32 in
Dimension - Length Overall inch	1.00 in

General

Trade Name	CRIMPIT™
Die Index	KR
Plated	Y
Color Code	Yellow
UPC	781810041802
Type	Compression Taps
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810041802
UPC 14 Digit GTIN	00781810041802

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3000
Carton Quantity	50

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

