



YHSA10K12, Heat Shrink Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K12](#)

Heat Shrink Ring Terminal For 12 - 10 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - L Length Overall mm	43 mm
Dimension - Pad Width inch	0.69 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13.00 mm
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	1/2 in
Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.36 in

General

Insulation Type	Heat Shrink
Trade Name	HYDENT™
Insulation	Y
Sub Brand	HYDENT
Physical Attribute - Tongue Type	Ring
Plated	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810477045
UPC 14 Digit GTIN	00781810477045
Material	Copper
Plating Type	Tin
UPC	781810477045

Logistics

Minimum Pack Quantity	100
Packaging Type	Bag
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)