



YHSA10K6, Heat Shrink Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K6](#)



Heat Shrink Ring Terminal For 12 - 10 AWG

Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Package Length	6.000 in
Package Width	3.900 in
Package Weight	0.200 lb.
Dimension - B Length inch	0.22 in

Dimension - Z inch	0.17 in
Dimension - L Length Overall mm	29 mm
Dimension - Pad Width inch	0.34 in
Package Height	0.600 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - Strip Length inch	11/32 in
Dimension - Stud Size inch	#4 - #6
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.17 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue Type	Ring
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810524664
UPC 14 Digit GTIN	00781810524664
Material	Copper
Plating Type	Tin
UPC	781810524664

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand