



YHSA10K8, Heat Shrink Ring Terminal For 12 - 10 AWG

By Burndy
Catalog # [YHSA10K8](#)

Heat Shrink Ring Terminal For 12 - 10 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - L Length Overall mm	30 mm
Dimension - Pad Width inch	0.29 in
Package Height	0.000 in
Dimension - Hole Size fraction	7/50
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4.00 mm
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#6 - #8
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#6 - #8
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.14 in

General

Insulation Type	Heat Shrink
Trade Name	HYDENT™
Insulation	Y
Sub Brand	HYDENT
Physical Attribute - Tongue Type	Ring
Plated	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810524701
UPC 14 Digit GTIN	00781810524701
Material	Copper
Plating Type	Tin
UPC	781810524701

Logistics

Minimum Pack Quantity	50
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)