



YHSA14K10, Heat Shrink Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YHSA14K10](#)

Heat Shrink Ring Terminal For 16 - 14 AWG

Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Standards - RoHS Compliance Status	CM

Conductor

Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Package Weight	0.000 lb.
Dimension - L Length Overall mm	30 mm
Dimension - Pad Width inch	0.32 in
Package Height	0.000 in
Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Hole Size mm	5 mm
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#10
Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	#10
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.17 in

General

Insulation Type	Heat Shrink
Trade Name	HYDENT™
Insulation	Y
Sub Brand	HYDENT
Physical Attribute - Tongue Type	Ring
Plated	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810476987
UPC 14 Digit GTIN	00781810476987
Material	Copper
Plating Type	Tin
UPC	781810476987

Logistics

Minimum Pack Quantity	100
Packaging Type	Bag
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)