




YGIBW346752N Structural Steel Compression Grounding Connector

By Burndy
Catalog # [YGIBW346752N](#)



GROUNDLINK™ Connector for Structural Steel Angled (Type YGIBS) or Parallel Beam (Type YGIBW)

Features

- Irreversible compression ground connector allowing attachment to a structural steel standard (Angled) or wide flange (Parallel) beam
- Made of high conductivity wrought copper and prefilled with PENETROX™ E compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • IEEE 837
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • IEEE 837
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	250 kcmil-500 kcmil
Conductor - Copper Str Size	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil

Configuration

Physical Attribute - Number of Tapped Holes	2
Connector Type	Tap

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	6 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	152 mm
Dimension - B Length inch	6.00 in
Dimension - I Beam Thickness inch	0.613" - 0.675"
Dimension - I Beam Thickness Range inch	• 0.563 • 0.600 • 0.625 • 0.575
Dimension - Length Overall inch	6.00 in

General

Plated	N
Trade Name	GROUNDLINK™
I Beam Style	Wide Flange Beam (Flange Parallel)
UPC	781810039441
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810039441
UPC 14 Digit GTIN	00781810039441

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1044
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)