



YGS34 Compression Grounding Splice, 500 kcmil Cu

By Burndy
Catalog # [YGS34](#)

HYGROUND® Grounding Irreversible Compression Splice



Features

- Irreversible compression ground splices specifically designed for grounding applications
- Each conductor element has an inspection probe hole and a center stop to ensure proper cable insertion
- UL467 Listed
- Acceptable for direct burial in earth or concrete
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL 486A-486B • UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil

Configuration

Physical Attribute - Number of Crimps Required	4
--	---

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-1/5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	118 mm
Dimension - B Length inch	2.20 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Length Overall inch	4.63 in

General

Plated	N
Trade Name	HYLINK™
Die Index	20
UPC	781810220443
Type	Splices
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810220443
UPC 14 Digit GTIN	00781810220443

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3456
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)