



## YH292CWC, Cu Compression H Tap and Cover, 250 kcmil-2 AWG Run, 2-14 AWG Tap

By Burndy

Catalog # [YH292CWC](#)

Copper Compression H Tap, 250 kcmil-2 AWG (Main), 2 AWG-14 AWG (Tap), Tin Plated



### Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

### Application

Wire Tap

### Specifications

|                                    |              |
|------------------------------------|--------------|
| Certification - UL Recognized      | No           |
| Buy American Compliant             | No           |
| Certification - cULus              | No           |
| EU RoHS Indicator                  | Yes          |
| Industry Standard(s)               | UL 486A-486B |
| Certification - ETL                | No           |
| Standards - RoHS Compliance Status | CM           |
| UL Listed                          | Yes          |
| Certification - CSA Approved       | Yes          |

### Conductor

|                               |                                                                                                                             |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Conductor - Material          | COPPER                                                                                                                      |
| Conductor - Copper Flex K Tap | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li><li>• 3</li><li>• 2</li></ul> |
| Conductor - Copper Flex M Run | <ul style="list-style-type: none"><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li></ul>     |

|                                     |                                                                                                                                       |
|-------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Flex I Tap Range | 2 AWG-8 AWG                                                                                                                           |
| Conductor - Copper Flex I Tap       | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li><li>• 3</li><li>• 2</li></ul>           |
| Conductor - Copper Flex K Run       | <ul style="list-style-type: none"><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li></ul>               |
| Conductor - Copper Flex G Run       | <ul style="list-style-type: none"><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li></ul>               |
| Conductor - Copper Str Run Range    | 250 KCMIL-2 AWG                                                                                                                       |
| Conductor - Copper Str Run          | <ul style="list-style-type: none"><li>• 2</li><li>• 1</li><li>• 1/0</li><li>• 2/0</li><li>• 3/0</li><li>• 4/0</li><li>• 250</li></ul> |
| Conductor - Copper Flex G Tap       | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li><li>• 3</li><li>• 2</li></ul>           |
| Conductor - Copper Flex M Tap       | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li><li>• 3</li><li>• 2</li></ul>           |
| Conductor - Copper Solid Tap        | <ul style="list-style-type: none"><li>• 6</li><li>• 5</li></ul>                                                                       |

|                                  |                                                                                                                             |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
|                                  | <ul style="list-style-type: none"><li>• 4</li><li>• 3</li><li>• 2</li></ul>                                                 |
| Conductor Type                   | CODE/FLEX                                                                                                                   |
| Conductor - Copper Flex H Tap    | <ul style="list-style-type: none"><li>• 8</li><li>• 7</li><li>• 6</li><li>• 5</li><li>• 4</li><li>• 3</li><li>• 2</li></ul> |
| Conductor - Copper Flex I Run    | 4/0 AWG-2 AWG                                                                                                               |
| Conductor - Copper Str Tap Range | 2 AWG-6 AWG                                                                                                                 |

Configuration

|                |                   |
|----------------|-------------------|
| Connector Type | H-TAP W/BLK COVER |
|----------------|-------------------|

Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 23 mm     |

|                                 |         |
|---------------------------------|---------|
| Dimension - Strip Length inch   | 1-1/16  |
| Dimension - Width inch          | 1.52 in |
| Dimension - Length Overall inch | 0.90 in |

General

|                   |                      |
|-------------------|----------------------|
| Trade Name        | CRIMPIT™             |
| Die Index         | 654                  |
| Plated            | Y                    |
| Color Code        | Purple               |
| Sub Brand         | CRIMPIT              |
| UPC               | 781810000298         |
| Type              | Compression Taps     |
| Material          | Copper               |
| Plating Type      | Tin - Electro Plated |
| Finish Type       | Tin-Plated           |
| UPC 12 Digit      | 781810000298         |
| UPC 14 Digit GTIN | 00781810000298       |

Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2250 |
| Carton Quantity       | 25   |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

[Catalog \[English\]](#)

