



YHSA14K8F, Heat Shrink Fork Terminal For 16 - 14 AWG

By Burndy
Catalog # [YHSA14K8F](#)

Heat Shrink Fork Terminal For 16 - 14 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Solid Size	• 16 AWG • 15 AWG • 14 AWG
Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 AWG • 14 AWG
Conductor - Copper Str Size Range	16 AWG - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	30 mm
Dimension - Pad Width inch	0.34 in
Package Height	0.000 in
Dimension - Bolt Size fraction	#8
Dimension - Strip Length inch	5/16 in
Dimension - Stud Size inch	#8
Dimension - Length Overall	1.17 in
inch	
Dimension - N inch	0.17 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue	Fork
Type	
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 12 Digit	781810524831
UPC 14 Digit GTIN	00781810524831
Material	Copper
Plating Type	Tin
UPC	781810524831

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)