




YH3434, Compression H-Tap

By Burndy
Catalog # [YH3434](#)

Copper Compression H Tap, 500 KCMIL-250 KCMIL (Main), 500 KCMIL-4/0 AWG(Tap), Tin Plated



Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

Application

Wire Tap

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Flex K Tap Range	4/0 AWG-350 kcmil
Conductor - Copper Flex K Tap	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil
Conductor - Copper Flex M Run Range	4/0 AWG-350 kcmil
Conductor - Copper Flex M Run	• 4/0 AWG • 250 kcmil • 300 kcmil • 350 kcmil

Conductor - Copper Flex I Tap Range 350 KCMIL-4/0 AWG

- Conductor - Copper Flex I Tap
- 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil

Conductor - Copper Flex K Run Range 4/0 AWG-350 kcmil

- Conductor - Copper Flex K Run
- 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil

Conductor - Copper Flex G Run Range 4/0 AWG-350 kcmil

- Conductor - Copper Flex G Run
- 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil

Conductor - Copper Flex H Run Range 350 kcmil

Conductor - Copper Flex H Run 350 kcmil

Conductor - Copper Str Run Range 500 KCMIL-250 KCMIL

Conductor - Copper Flex G Tap Range 4/0 AWG-350 kcmil

- Conductor - Copper Str Run
- 250 kcmil
 - 300 kcmil
 - 350 kcmil
 - 400 kcmil
 - 450 kcmil
 - 500 kcmil
- Conductor - Copper Flex G Tap
- 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil

Conductor - Copper Flex M Tap Range 4/0 AWG-350 kcmil

- Conductor - Copper Flex M Tap
- 4/0 AWG
 - 250 kcmil
 - 300 kcmil
 - 350 kcmil

Conductor - Copper Flex H Tap Range 4/0 AWG-350 kcmil

- Conductor Type CODE/FLEX
- Conductor - Copper Flex H Tap
- 4/0 AWG
 - 250 kcmil
 - 300 kcmil

Conductor - Copper Flex I Run Range	• 350 kcmil
	4/0 AWG-350 kcmil
Conductor - Copper Flex I Run	350 KCMIL-4/0 AWG
Conductor - Copper Str Tap Range	500 KCMIL-4/0 AWG
Conductor - Copper Str Tap	• 4/0 AWG
	• 250 kcmil
	• 300 kcmil
	• 350 kcmil
	• 400 kcmil
	• 450 kcmil
	• 500 kcmil

Configuration

Connector Type	H-TAP
----------------	-------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - Height inch	2.43 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	25 mm

mm

Dimension - Width fraction	1.15 in
Dimension - Strip Length inch	1-1/8
Dimension - Width inch	2.43 in
Dimension - Length Overall	1.00 in
inch	

General

Trade Name	CRIMPIT™
Die Index	1104
Plated	Y
Color Code	Brown
Sub Brand	CRIMPIT
UPC	781810144213
Type	Compression Taps
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810144213
UPC 14 Digit GTIN	00781810144213

Logistics

Minimum Pack Quantity	1
-----------------------	---

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

