



## YH3939WCC, Cu Compression H Tap and Clear Cover, 750-500 kcmil Run, 750-350 kcmil Tap

By Burndy

Catalog # [YH3939WCC](#)

Copper Compression H Tap, 750 KCMIL-500 KCMIL (Main), 750 KCMIL-350 KCMIL (Tap), Tin Plated

### Features

- Uninsulated compression H-tap connector, tin-plated
- Designs with more than one tap wire groove require installers to utilize a minimum of one Main (Run) and one Tap groove, other grooves can be left empty
- 'Third Hand' is a string provided with the H-tap connector and is used to wrap the wire while being inserted into the run and tap grooves
- H-tap connectors can be purchased separately or kitted with covers
- YH is connector sold separately without cover
- YH-WC is kitted H-tap connector and black cover
- YH-WCC is kitted H-tap connector and clear cover

### Application

Wire Tap

### Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Certification - UL Recognized      | No                   |
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Buy America(n) Qualified           | Contact Manufacturer |
| Industry Standard(s)               | UL 486A-486B         |
| Certification - ETL                | No                   |
| Standards - RoHS Compliance Status | CM                   |
| UL Listed                          | Yes                  |
| Certification - CSA Approved       | Yes                  |

### Conductor

|                                     |                                                                                                 |
|-------------------------------------|-------------------------------------------------------------------------------------------------|
| Conductor - Material                | COPPER                                                                                          |
| Conductor - Copper Flex K Tap       | <ul style="list-style-type: none"><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li></ul> |
| Conductor - Copper Flex M Run       | <ul style="list-style-type: none"><li>• 450</li><li>• 500</li></ul>                             |
| Conductor - Copper Flex I Tap Range | 550 KCMIL-350 KCMIL                                                                             |
| Conductor - Copper Flex I Tap       | <ul style="list-style-type: none"><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li></ul> |



|                                  |                                                                                                                                           |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Flex K Run    | <ul style="list-style-type: none"><li>• 450</li><li>• 500</li></ul>                                                                       |
| Conductor - Copper Flex G Run    | <ul style="list-style-type: none"><li>• 450</li><li>• 500</li></ul>                                                                       |
| Conductor - Copper Str Run Range | 750 KCMIL-500 KCMIL                                                                                                                       |
| Conductor - Copper Str Run       | <ul style="list-style-type: none"><li>• 500</li><li>• 550</li><li>• 600</li><li>• 700</li><li>• 750</li></ul>                             |
| Conductor - Copper Flex G Tap    | <ul style="list-style-type: none"><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li></ul>                                           |
| Conductor - Copper Flex M Tap    | <ul style="list-style-type: none"><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li></ul>                                           |
| Conductor Type                   | CODE/FLEX                                                                                                                                 |
| Conductor - Copper Flex H Tap    | <ul style="list-style-type: none"><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li></ul>                                           |
| Conductor - Copper Flex I Run    | 550 KCMIL-450 KCMIL                                                                                                                       |
| Conductor - Copper Str Tap Range | 750 KCMIL-350 KCMIL                                                                                                                       |
| Conductor - Copper Str Tap       | <ul style="list-style-type: none"><li>• 350</li><li>• 400</li><li>• 450</li><li>• 500</li><li>• 550</li><li>• 600</li><li>• 700</li></ul> |

### Configuration

|                |                   |
|----------------|-------------------|
| Connector Type | H-TAP W/CLR COVER |
|----------------|-------------------|

### Current

|                   |       |
|-------------------|-------|
| Voltage Rating    | 35 kV |
| Voltage - Maximum | 35000 |

### Dimensions

|                |           |
|----------------|-----------|
| Package Height | 0.000 in  |
| Package Weight | 0.000 lb. |

Package Length 0.000 in  
Package Width 0.000 in  
Dimension - L Length Overall 32 mm  
mm  
Dimension - Strip Length inch 1-3/8  
Dimension - Width inch 2.97 in  
Dimension - Length Overall 1.25 in  
inch

General

Trade Name CRIMPIT™  
Die Index KR  
Plated Y  
Color Code Yellow  
Sub Brand CRIMPIT  
UPC 781810436493  
Type Compression Taps

Material Copper  
Plating Type Tin - Electro Plated  
Finish Type Tin-Plated  
UPC 12 Digit 781810436493  
UPC 14 Digit GTIN 00781810436493

Logistics

Minimum Pack Quantity 1  
Pallet Quantity 450  
Carton Quantity 5

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)



A Hubbell brand