



YHSA18K38, Heat Shrink Ring Terminal For 22 - 18 AWG

By Burndy
Catalog # [YHSA18K38](#)

Heat Shrink Ring Terminal For 22 - 18 AWG

Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.

Dimension - L Length Overall mm	37 mm
Dimension - Pad Width inch	0.56 in
Package Height	0.000 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	3/8
Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.45 in
Dimension - N inch	0.28 in

General

Insulation Type	Heat Shrink
Trade Name	HYDENT™
Insulation	Y
Sub Brand	HYDENT
Physical Attribute - Tongue Type	Ring
Plated	Y
Type	YHS, Heat Shrink
UPC 14 Digit GTIN	00781810476963
Material	Copper
Plating Type	Tin
UPC	781810476963

Logistics

Minimum Pack Quantity	100
Packaging Type	Bag
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)