



YHSA18K6BF, Heat Shrink Block Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YHSA18K6BF](#)



Heat Shrink Block Fork Terminal For 22 - 18 AWG

Features

- Permits rapid, easy installation of the terminal under the screw head without complete removal of the screw
- Designed to fit securely into terminal blocks

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Block Fork Terminal
----------------	---------------------

Dimensions

Dimension - Z inch	0.32 in
--------------------	---------

Dimension - L Length Overall mm	30 mm
Dimension - Pad Width inch	0.25 in
Dimension - Bolt Size fraction	#4 - #6
Dimension - Strip Length inch	7/32 in
Dimension - Stud Size inch	• #4 • #5 • #6
Dimension - Length Overall inch	1.20 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue Type	Block Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 14 Digit GTIN	00781810524879
Material	Copper
Plating Type	Tin
UPC	781810524879

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)