



YHSA14K6, Heat Shrink Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [YHSA14K6](#)

Heat Shrink Ring Terminal For 16 - 14 AWG

Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Ring Terminal
----------------	---------------

Dimensions

Dimension - B Length inch	0.22 in
Dimension - L Length Overall mm	30 mm
Dimension - Pad Width inch	0.30 in
Dimension - Bolt Size fraction	#6
Dimension - Hole Size inch	0.14 in
Dimension - Hole Size mm	4 mm
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.15 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue Type	Ring
Trade Name	HYDENT™
Type	YHS, Heat Shrink
UPC 12 Digit	781810524787
UPC 14 Digit GTIN	00781810524787
Material	Copper
UPC	781810524787

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)