



YHSS18, Heat Shrink Splice For 22 - 18 AWG

By Burndy
Catalog # [YHSS18](#)

Heat Shrink Splice For 22 - 18 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Dimensions

Package Length	4.000 in
Package Width	3.000 in
Dimension - B Length fraction	1/4 in
Package Weight	3.000 lb.
Dimension - B Length inch	0.25 in
Dimension - L Length Overall mm	38 mm
Package Height	3.500 in
Dimension - Strip Length inch	5/16
Dimension - Length Overall inch	1.50 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 14 Digit GTIN	00781810476895
Material	Copper
Plating Type	Tin
UPC	781810476895

Logistics

Minimum Pack Quantity	100
Packaging Type	Bag
Carton Quantity	100
Pallet Quantity	1000

Product Assets

[Catalog \[English\]](#)