



YNA39RT15H, Aluminum Terminal, 15° Angle

By Burndy
Catalog # [YNA39RT15H](#)



Four hole compression terminal, Extra high voltage applications

Features

- Aluminum Compression Terminal
- 15 Degree Angle
- 4-Hole

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	634.9 - 653.1 KCMIL
Conductor - ACAR Str Size	634.9 - 653.1 KCMIL
Conductor - AL Str Size	• 600 kcmil • 636 kcmil • 650 kcmil
Conductor - AL Str Size Range	600 kcmil-650 kcmil
Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil • 556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (30/7) Eagle kcmil

Configuration

Physical Attribute - Pad Orientation	15 Degree
--------------------------------------	-----------

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	2.08 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	255 mm
Dimension - Outside Diameter inch	1.5 in
Dimension - Width fraction	2.08 in
Dimension - Length Overall inch	10.02 in

General

Die Index	722
UPC	781810136775
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810136775
UPC 14 Digit GTIN	00781810136775

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1350
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)



A Hubbell brand