



YNA451R2N, 2-hole Aluminum Terminal

By Burndy
Catalog # [YNA451R2N](#)

HYLUG™, Aluminum Compression Terminal of operating voltage 230 Kv, 715.5-874.5 Kcmil ACSR, 795-1000 Kcmil Alum., 840.2-927.2 Kcmil ACAR

Features

- Aluminum Compression Terminal
- 2-Hole Pad

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	840.2 KCMIL - 927.2 KCMIL
Conductor - ACAR Str Size	840.2 KCMIL - 927.2 KCMIL
Conductor - AL Str Size	795.5 800 874.5 900 954 1000
Conductor - AL Str Size Range	795.5-1000
Conductor - ACSR Str Size	715.5 (54/7) Crow 715.5 (26/7) Starling 715.5 (30/19) Redwing 795 (54/7) Condor 795 (26/7) Drake 795 (30/19) Mallard 874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	2.5 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	261 mm
Dimension - Outside Diameter inch	1.8 in
Dimension - Width fraction	2.50 in
Dimension - Length Overall inch	10.28 in

General

Trade Name	HYLUG™
Die Index	725
UPC	781810180297
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180297
UPC 14 Digit GTIN	00781810180297

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)