



YNA49RTDT, Aluminum Terminal, 4-hole

By Burndy
Catalog # [YNA49RTDT](#)

HYLUG™, Aluminum Compression terminal, 900-1113 Kcmil ACSR,1033.5-1272 Kcmil Alum.,983.1-1198 Kcmil ACAR, Cable to flat, 4 hole



Features

- Aluminum Compression Terminal
- 4-Hole Pad
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	983.1 KCMIL - 1198 KCMIL
Conductor - ACAR Str Size	983.1 KCMIL - 1198 KCMIL
Conductor - AL Str Size	1033.5 1100 1192.5 1200 1272.2
Conductor - AL Str Size Range	1033.5-1272.2
Conductor - ACSR Str Size	900 (54/7) Canary 954 (54/7) Cardinal 1033.5 (54/7) Curlew 1113 (54/19) Finch
Conductor - ACSR Str Size Range	900 (54/7) Canary-1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	274 mm
Dimension - Outside Diameter inch	1.97 in
Dimension - Width fraction	3.22 in
Dimension - Length Overall inch	10.77 in

General

Trade Name	HYLUG™
Die Index	727
UPC	781810330609
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810330609
UPC 14 Digit GTIN	00781810330609

Logistics

Minimum Pack Quantity	1
Pallet Quantity	720
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)