



YHSA18K6F, Heat Shrink Fork Terminal For 22 - 18 AWG

By Burndy
Catalog # [YHSA18K6F](#)

Heat Shrink Fork Terminal For 22 - 18 AWG



Features

- Made from pure copper, annealed for maximum strength
- Color-coded, imprinted with wire size
- Serrated barrels offer maximum wire contact and tensile strength
- Electro-tin plated for corrosion resistance

Application

For Use On Copper Conductor

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor Size	22 - 18 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Fork Terminal
----------------	---------------

Dimensions

Dimension - L Length Overall mm	30 mm
Dimension - Pad Width inch	0.25 in
Dimension - Bolt Size fraction	#6
Dimension - Strip Length inch	5/16
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	1.17 in
Dimension - N inch	0.17 in

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Physical Attribute - Tongue Type	Fork
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YHS, Heat Shrink
UPC 14 Digit GTIN	00781810524886
Material	Copper
Plating Type	Tin
UPC	781810524886

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)