

YNA32R15, ACSR - 15 Degree Compression Terminal

By Burndy
Catalog # [YNA32R15](#)



Al Tube Compression Terminal, 15 Deg Bent, 2 Holes, 300 - 336.4 Kcmil ACSR, 336.4 - 350 Kcmil Al, 395.1 - 395.2 Kcmil ACAR, 230 kV, 1.75" Spacing

Features

- ACSR Compression Terminal, 15 Degree Bend
- 2-Hole Pad

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	395.1-395.2
Conductor - ACAR Str Size	395.1-395.2
Conductor - ACSR Str Size	• 336.4 (26/7) Linnet kcmil • 336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet kcmil-336.4 (30/7) Oriole kcmil

Configuration

Physical Attribute - Pad Orientation	15 Degree
Physical Attribute - Number of Holes	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.68 in
Package Height	0.000 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	233 mm
Dimension - Outside Diameter inch	1.19 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - Length Side A inch	8.92 in
Dimension - Length Side B inch	8.96 in
Dimension - Length Overall inch	9.16 in

General

Trade Name	HYLUG™
Die Index	717
Prefilled Oxide Inhibitor	Y
Feature - Barrel Type	Long
Feature - Barrel Style	Tapered
Plated	N
UPC	781810016329
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810016329
UPC 14 Digit GTIN	00781810016329

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)