



YNA52RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA52RT](#)



HYLUG™, Aluminum Tube Compression Terminal, 4 Holes, 1113.54-19 Str Kcmil ACSR, 1351.5 - 1510 Kcmil Al, 1277 - 1280 Kcmil ACAR, greater than 230 kV, 1.75" Spacing

Features

- ACSR Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	1277 KCMIL- 1280 KCMIL
Conductor - ACAR Str Size	1277 KCMIL- 1280 KCMIL
Conductor - AL Str Size	• 1351.5 • 1400 • 1431.0 • 1500
Conductor - AL Str Size Range	1351.5-1500
Conductor - ACSR Str Size	1113 (54/19) Finch
Conductor - ACSR Str Size Range	1113 (54/19) Finch

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	351 mm
Dimension - Outside Diameter inch	2.25 in
Dimension - Width fraction	3.22 in
Dimension - Length Overall inch	13.82 in

General

Trade Name	HYLUG™
Die Index	728
UPC	781810016381
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016381
UPC 14 Digit GTIN	00781810016381

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)