



YNA36R45, Aluminum Terminal 45° Angle

By Burndy
Catalog # [YNA36R45](#)

Aluminum Compression Terminal 230 kV, 477 kcmil ASCR, 500-556.5 kcmil Alum., 45 Deg



Features

- Aluminum Compression Terminal
- 45 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	500 550 556.5
Conductor - AL Str Size Range	500-556.5
Conductor - ACSR Str Size	477.0 (18/1) Pelican 477.0 (24/7) Flicker 477.0 (26/7) Hawk 477.0 (30/7) Hen
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican-477.0 (30/7) Hen

Configuration

Physical Attribute - Pad Orientation	45 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.96 in
Dimension - Height inch	5.71 in
Dimension - Height fraction	5-22/31 in
Dimension - L Length Overall mm	209 mm
Dimension - B Length inch	4.47 in
Dimension - Outside Diameter inch	1.41 in
Dimension - Length Overall inch	8.23 in

General

Trade Name	HYLUG™
Die Index	720
UPC	781810283912
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810283912
UPC 14 Digit GTIN	00781810283912

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)