



YNA451RT15TN, Aluminum Terminal, 15° Angle

By Burndy
Catalog # [YNA451RT15TN](#)

HYLUG™, Aluminum Compression Terminal, 715.5-874.5 Kcmil ACSR, 795-1000 Kcmil Aluminum, 840-927.2 Kcmil ACAR,15 Degree, Tin Plated



Features

- Aluminum Compression Terminal
- 15 Degree Angle
- Tin Plated

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	840.2 KCMIL - 927.2 KCMIL
Conductor - ACAR Str Size	840.2 KCMIL - 927.2 KCMIL
Conductor - AL Str Size	• 795.5 • 800 • 874.5 • 900 • 954 • 1000
Conductor - AL Str Size Range	795 -1000
Conductor - ACSR Str Size	• 715.5 (54/7) Crow • 715.5 (26/7) Starling • 715.5 (30/19) Redwing • 795 (54/7) Condor • 795 (26/7) Drake • 795 (30/19) Mallard • 874.5 (54/7) Crane
Conductor - ACSR Str Size Range	715.5 (54/7) Crow-874.5 (54/7) Crane

Configuration

Physical Attribute - Pad Orientation	15 Degree
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.22 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	271 mm
Dimension - Outside Diameter inch	1.8 in
Dimension - Width fraction	3.22 in
Dimension - Length Overall inch	10.65 in

General

Trade Name	HYLUG™
Die Index	725
UPC	781810246290
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Tin Plated
UPC 12 Digit	781810246290
UPC 14 Digit GTIN	00781810246290

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)