



YNA58RT, Aluminum Terminal

By Burndy
Catalog # [YNA58RT](#)



HYLUG™, Al Tube Compression Terminal, operates 345 Kv, 1780 Kcmil ACSR, 2000 Kcmil Aluminum, Cable to flat, For use on extrahigh voltage applications

Features

- Aluminum Compression Terminal
- For use on Extra High Voltage Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2000 kcmil
Conductor - AL Str Size Range	2000 kcmil
Conductor - ACSR Str Size	1780 (54/19) kcmil
Conductor - ACSR Str Size Range	1780 (54/19) kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.47 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in

Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	348 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Width fraction	3.47 in
Dimension - Length Overall inch	13.7 in

General

Trade Name	HYLUG™
Die Index	735
UPC	781810164556
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810164556
UPC 14 Digit GTIN	00781810164556

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)