



YNA594RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA594RT](#)

HYLUG™, Al Tube Compression Terminal, 4 Holes, 2300 Kcmil
ACSR, 2500 Kcmil Al, 2267-2500 Kcmil ACAR, 1.75" Spacing



Features

- ACSR Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size Range	2267 KCML - 2500 KCMIL
Conductor - ACAR Str Size	2267 KCML - 2500 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL

Configuration

Physical Attribute - Pad Orientation	Straight
Physical Attribute - Number of Holes	4
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.7 in
Dimension - Bolt Hole Size inch	0.56 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	357 mm
Dimension - Outside Diameter inch	2.6 in
Dimension - Width fraction	3.70 in
Dimension - Length Overall inch	14.06 in

General

Trade Name	HYLUG™
Die Index	740
UPC	781810016176
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016176
UPC 14 Digit GTIN	00781810016176

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)