



YNA594RT90, Aluminum Terminal, 90° Angle

By Burndy
Catalog # [YNA594RT90](#)

Aluminum Compression terminal, 2156-2167 kcmil, 345 kV



Features

- Aluminum Compression Terminal
- 90 Degree Angle

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	2500
Conductor - AL Str Size Range	2500
Conductor - ACSR Str Size	2300
Conductor - ACSR Str Size Range	2300

Configuration

Physical Attribute - Pad Orientation	90 Degree Angle
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.75 in
Dimension - L Length Overall mm	242 mm
Dimension - B Length inch	7.88 in
Dimension - Outside Diameter inch	2.6 in
Dimension - Length Overall inch	9.53 in

General

Trade Name	HYLUG™
UPC	781810180488
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180488
UPC 14 Digit GTIN	00781810180488

Logistics

Minimum Pack Quantity	1
Pallet Quantity	180
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)