



YNA7M10TH, Alumoweld - EHS Steel Compression Terminal

By Burndy
Catalog # [YNA7M10TH](#)

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #10, 3 #7 Alumoweld, 5/16 Steel, 7 Str., H/W Kit is available

Features

- Alumoweld-EHS Steel Compression Terminal

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel Str Size	5/16 (7) in
Conductor - Galvanized Steel Str Size Range	5/16 (7) in
Conductor Type	GAL Steel C Str-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.5 in
Dimension - Bolt Hole Size inch	0.56 in



Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	216 mm
Dimension - B Length inch	2.68 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Length Overall inch	8.5 in

General

Die Index	676 721
UPC	781810180518
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180518
UPC 14 Digit GTIN	00781810180518

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)