

YNA59R, Aluminum Terminal

By Burndy
Catalog # [YNA59R](#)



HYLUG™, Aluminum Compression terminal for ACSR, Aluminum, ACAR transmission lines, 2156-2167 Kcmil ACSR, 2250-2300 Kcmil Aluminum, Tube to flat, 4 Pad holes

Features

- Aluminum Compression Terminal
- 4-Hole Pad

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2250 kcmil • 2300 kcmil
Conductor - AL Str Size Range	• 2250 kcmil • 2300 kcmil
Conductor - ACSR Str Size	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	3.57 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	337 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Width fraction	3.57 in
Dimension - Length Overall inch	13.25 in

General

Trade Name	HYLUG™
Die Index	735
UPC	781810460528
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810460528
UPC 14 Digit GTIN	00781810460528

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)