



YNA7M7T, Alumoweld - EHS Steel Compression Terminal

By Burndy
Catalog # [YNA7M7T](#)

Steel Compression terminal for Alumoweld and EHS Steel to dead end, 7 #7 Alumoweld, 7/16 Steel, 7 Str.

Features

- Alumoweld-EHS Steel Compression Terminal

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel Str Size	7/16 (7) in
Conductor - Galvanized Steel Str Size Range	7/16 (7) in
Conductor Type	GAL Steel C Str-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.5 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in

Dimension - L Length Overall mm	253 mm
Dimension - B Length inch	4.19 in
Dimension - Outside Diameter inch	1.00 in
Dimension - Length Overall inch	9.95 in

General

Die Index	678 726
UPC	781810180525
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810180525
UPC 14 Digit GTIN	00781810180525

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)