

## YPC36A36, Figure 6-shaped Connector

By Burndy

Catalog # [YPC36A36](#)

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:397.5 (19) - 600 (61)



### Features

- Figure 6-Shaped Connector
- Separates Run and Tap Wires

### Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | CM |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

### Conductor

|                                  |                                                                                                                                                                                                                  |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Run Range | 397 kcmil-600 kcmil                                                                                                                                                                                              |
| Conductor - Copper Str Run       | <ul style="list-style-type: none"> <li>• 397 kcmil</li> <li>• 400 kcmil</li> <li>• 450 kcmil</li> <li>• 477 kcmil</li> <li>• 500 kcmil</li> <li>• 550 kcmil</li> <li>• 556 kcmil</li> <li>• 600 kcmil</li> </ul> |
| Conductor - AL Str Run Range     | 397 kcmil-600 kcmil                                                                                                                                                                                              |
| Conductor - AL Str Run           | <ul style="list-style-type: none"> <li>• 397 kcmil</li> <li>• 400 kcmil</li> <li>• 450 kcmil</li> <li>• 477 kcmil</li> <li>• 500 kcmil</li> <li>• 550 kcmil</li> <li>• 556 kcmil</li> <li>• 600 kcmil</li> </ul> |
| Conductor - AL Str Tap Range     | 397 kcmil-600 kcmil                                                                                                                                                                                              |
| Conductor - AL Str Tap           | <ul style="list-style-type: none"> <li>• 397 kcmil</li> <li>• 400 kcmil</li> <li>• 450 kcmil</li> <li>• 477 kcmil</li> <li>• 500 kcmil</li> <li>• 550 kcmil</li> <li>• 556 kcmil</li> <li>• 600 kcmil</li> </ul> |
| Conductor Type                   | <ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• CU C Solid-Run</li> </ul>                                                                                               |

|                                  |                                                                                                                                                                                                                  |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACSR Str Run Range   | 336.4 kcmil-556.5 kcmil                                                                                                                                                                                          |
| Conductor - Copper Str Tap Range | 397 kcmil-600 kcmil                                                                                                                                                                                              |
| Conductor - Copper Str Tap       | <ul style="list-style-type: none"> <li>• 397 kcmil</li> <li>• 400 kcmil</li> <li>• 450 kcmil</li> <li>• 477 kcmil</li> <li>• 500 kcmil</li> <li>• 550 kcmil</li> <li>• 556 kcmil</li> <li>• 600 kcmil</li> </ul> |
| Conductor - ACSR Str Tap Range   | 336.4 kcmil-556.5 kcmil                                                                                                                                                                                          |

### Dimensions

|                                 |           |
|---------------------------------|-----------|
| Package Height                  | 0.000 in  |
| Dimension - Height inch         | 3.70 in   |
| Package Weight                  | 0.000 lb. |
| Dimension - Width inch          | 1.88 in   |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 171 mm    |
| Dimension - Length Overall inch | 6.75 in   |

### General

|                   |                |
|-------------------|----------------|
| Plated            | N              |
| Trade Name        | CRIMPIT™       |
| Die Index         | Z              |
| UPC               | 781810138601   |
| Material          | Aluminum       |
| Plating Type      | Unplated       |
| UPC 12 Digit      | 781810138601   |
| UPC 14 Digit GTIN | 00781810138601 |

### Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 396 |
| Carton Quantity       | 9   |



A Hubbell brand