



YNA59RT, ACSR - Compression Terminal

By Burndy
Catalog # [YNA59RT](#)

HYLUG™, Al Tube Compression Terminal, 4 Holes, 2156 -2167 Kcmil ACSR, 2250 - 2300 Kcmil Al, greater than 230 kV, 1.75" Spacing.

Features

- Compression Terminal with 4-hole pad

Application

For ACAR And Stranded Aluminum Cable

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 2250 kcmil • 2300 kcmil
Conductor - AL Str Size Range	• 2250 kcmil • 2300 kcmil
Conductor - ACSR Str Size	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil
Conductor - ACSR Str Size Range	• 2156 (84/19) Bluebird kcmil • 2167 (72/7) Kiwi kcmil

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions



Dimension - Pad Width inch	3.57 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	344 mm
Dimension - Outside Diameter inch	2.5 in
Dimension - Width fraction	3.57 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Length Overall inch	13.54 in

General

Trade Name	HYLUG™
Die Index	735
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
UPC	781810016466
Type	YNA-RT
Material	Aluminum
UPC 12 Digit	781810016466
UPC 14 Digit GTIN	00781810016466

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)