

YRAL1CU, Aluminum Lug, Prefilled with Oxide Inhibitor

By Burndy
Catalog # [YRAL1CU](#)



AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX

Features

- Aluminum HYLUG for joining aluminum and copper cable to transformer and equipment pads
- Pre-filled with PENETROX Joint Compound and Capped

Application

For Joining Aluminum And Copper Cable To Transformer And Equipment Pads

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	• 2 AWG • 1 AWG
Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	• 2 AWG • 1 AWG
Conductor - AL Str Size Range	2 AWG - 1 AWG
Conductor - Copper Str Size Range	2 AWG - 1 AWG

Configuration

Physical Attribute - Pad Configuration	1 Hole
--	--------

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.91 in
Dimension - L Length Overall mm	81 mm
Dimension - Pad Width inch	0.91 in
Package Height	0.000 in
Dimension - Strip Length inch	1 1/2 in
Thickness - Pad	0.25 in
Dimension - B Length fraction	3-1/4 in
Dimension - B Length inch	1.43 in
Physical Attribute - Tongue Angle	Straight
Dimension - Length Overall inch	3.19 in
Dimension - D inch	1.28 in
Dimension - N inch	0.62 in

General

Die Index	• 249 • K-840
Trade Name	HYLUG™
Prefilled Oxide Inhibitor	Y
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Standard
Plated	N
Construction Material - Main Type	Aluminum YRA
UPC 12 Digit	781810810125
UPC 14 Digit GTIN	00781810810125
Material	Aluminum
Plating Type	Unplated
UPC	781810810125

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	14800

Product Assets

[Catalog \[English\]](#)