



YNA7M8T, Alumoweld - EHS Steel Compression Terminal

By Burndy
Catalog # [YNA7M8T](#)

Al Comp Static Wire Terminal, 2 Hole, 7 #8, 3 #5(Alumoweld),
3/8" Steel, 7 Str, 7 #8, 3 #5(Alumoweld), 3/8" Steel, 7 Str



Features

- Compression Terminal, 2-hole pad

Application

For Alumoweld And EHS Steel

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel Str Size	3/8 (7) in
Conductor - Galvanized Steel Str Size Range	3/8 (7) in
Conductor Type	GAL Steel C Str-Size

Configuration

Physical Attribute - Pad Orientation	Straight
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.5 in
Package Height	0.000 in

Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Package Width	0.000 in
Dimension - L Length Overall mm	249 mm
Dimension - Outside Diameter inch	0.88 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - B Length inch	3.49 in
Dimension - Length Overall inch	9.81 in

General

Die Index	• 668 • 723
Material Type - Sleeve	Aluminum
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
UPC	781810016138
Type	YNA-M-T, Terminal
Construction Material - Main Material	Aluminum
UPC 12 Digit	781810016138
UPC 14 Digit GTIN	00781810016138

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)