



YRV4CV6CL, Uninsulated Reducing Splice
For 4 AWG and 6 AWG

By Burndy
Catalog # [YRV4CV6CL](#)

Uninsulated Reducing Splice For 4 AWG and 6 AWG, Pure Electrolytic Copper, Tin Plated

Features

- Constructed from pure electrolytic copper tubing for optimal conductivity
- Tin plated to resist corrosion

Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	6 AWG
Conductor - Copper Str Size B	6
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor - Copper Str Size	4
Conductor - Copper Flex H Size B Range	N/A

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
Length	1.24 in
Dimension - B Length fraction	1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.61 in
Dimension - B Outside Diameter inch	0.3 in
Dimension - A Outside Diameter inch	0.38 in
Dimension - Length BB inch	0.52 in
Dimension - Length Overall inch	1.24 in

General

Feature - Barrel Style	Chamfered
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYREDUCER™
Sub Brand	HYREDUCER
Product Type	Splice Reducer
UPC	781810085769
Type	Reducing Splices
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810085769

Logistics

Minimum Pack Quantity	100
Pallet Quantity	96000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)