



YRV6CV10L, Reducing Splice For 6 AWG and 12 - 10 AWG

By Burndy
Catalog # [YRV6CV10L](#)

Uninsulated Reducing Splice For 6 AWG and 12 - 10 AWG, Pure Electrolytic Copper, Tin Plated

Features

- Constructed from pure electrolytic copper tubing for optimal conductivity
- Tin plated to resist corrosion

Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	12 - 10 AWG
Conductor - Copper Str Size B	10
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor - Copper Str Size	6
Conductor - Copper Flex H Size B	N/A
Range	

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Height	0.000 in
Length	1.25 in
Dimension - B Length fraction	1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	0.50 in
Dimension - B Outside Diameter inch	0.21 in
Dimension - A Outside Diameter inch	0.3 in
Dimension - Length BB inch	0.53 in
Dimension - Length Overall inch	1.25 in

General

Feature - Barrel Style	Chamfered
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYREDUCER™
Sub Brand	HYREDUCER
Product Type	Splice Reducer
UPC	781810026373
Type	Reducing Splices
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810026373

Logistics

Minimum Pack Quantity	1
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)