



YRV8CV14L, Uninsulated Reducing Splice For 8 AWG and 20 - 14 AWG

By Burndy
Catalog # [YRV8CV14L](#)

Uninsulated Reducing Splice For 8 AWG and 20 - 14 AWG



Features

- Constructed from pure electrolytic copper tubing for optimal conductivity
- Tin plated to resist corrosion

Application

For Splicing Two Different Size Wires, Aircraft Applications (Flexible Cables)

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Conductor

Conductor - Copper Str Size B	14
Conductor Size	20 - 14 AWG
Conductor - Copper Str Size	8
Conductor - Copper Flex H Size	N/A
B Range	
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Reducer
----------------	---------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	7/16 in
Package Weight	0.000 lb.
Dimension - B Outside	0.16 in
Diameter inch	
Dimension - B Length inch	0.49 in
Package Height	0.000 in
Length	1.16 in
Dimension - Length BB inch	0.39 in
Dimension - Length Overall	1.16 in
inch	
Dimension - A Outside	0.27 in
Diameter inch	

General

Sub Brand	HYREDUCER
Trade Name	HYREDUCER™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Reducing Splices
UPC 14 Digit GTIN	00781810035924
Material	Copper
Plating Type	Tin
UPC	781810035924

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)