



YS44A2, Compression Splice, 1000 kcmil
AL, AL9CU

By Burndy
Catalog # [YS44A2](#)

1000 KCMIL, AL, SPLICE, AL9CU

Features

- Aluminum splices are dual rated to accommodate both copper and aluminum wire
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Clearly marked with wire size, die index, color code, and crimp location bands
- Factory pre-filled with PENETROX™ Type A13 oxide inhibitor
- Color coded end caps inserted in the barrels to match the die color code and prevent foreign materials from entering the barrel

Application

Wire Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	1000 KCMIL
Conductor - Material	ALUMINUM / COPPER
Wire Size	1000 KCMIL
Conductor - AL Str Size	1000 KCMIL
Conductor - AL Str Size Range	900 kcmil
Conductor Type	CODE
Conductor - Copper Str Size Range	1000 kcmil
Conductor - Copper Str Size	1000 KCMIL

Configuration

Connector Type	DUAL RATED
----------------	------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-3/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	127 mm
Dimension - B Length inch	2.35 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Length Overall inch	5.0 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Brown
Trade Name	HYLINK™
Die Index	302
UPC	781810091579
Material	Aluminum
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810091579
UPC 14 Digit GTIN	00781810091579

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1920
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand