




YSES14K, Radiation Resistant Insulated Splice For 16 - 14 AWG

By Burndy

Catalog # [YSES14K](#)

Radiation Resistant Insulated Splice For 16 - 14 AWG



Features

- Insulated splices suitable for Class 1E applications
- Pure electrolytic copper seamless tubing eliminates potential splitting of seams
- Color-coded stripe identifies wire size
- Window is provided for inspection of proper wire insertion
- Suitable for 200 Megarads Rated 60°C through 150°C
- 600 Volts

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	• 16 • 15 • 14
Conductor - Copper Solid Size Range	16-14
Conductor - Copper Str Aircraft Size	• AN 16 • AN 14
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 16 • 14
Conductor - Copper Str Size Range	16-14
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Length	0.000 in
----------------	----------



A Hubbell brand

Package Width	0.000 in
Dimension - B Length fraction	15/79 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.19 in
Dimension - Outside Diameter inch	0.25 in
Dimension - L Length Overall mm	25 mm
Dimension - P inch	0.04 in
Dimension - Pad Width inch	0.15 in
Package Height	0.000 in
Dimension - Strip Length inch	3/16 in
Cable Insulation Diameter Maximum	0.153 in
Dimension - Length Overall inch	1.00 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - N inch	0.16 in

General

Insulation Type	Radiation Resistant
Color Code	Blue
Trade Name	INSULINK™
Plated	Y
Insulation Type	Y
	Radiation Resistant KYNAR Splice
UPC 12 Digit	781810085776
UPC 14 Digit GTIN	00781810085776
Material	Copper
Plating Type	Tin
UPC	781810085776

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Operational

Temperature Rating	150
--------------------	-----

Product Assets

[Catalog \[English\]](#)