


YSE14HHS, Heat Shrink Splice For 16 - 14 AWG

By Burndy
Catalog # [YSE14HHS](#)

Heat Shrink Splice For 16 - 14 AWG



Features

- Manufactured from tin plated, seamless electrolytic copper tubing with integral barrel for maximum conductivity and tensile strength, plus excellent cable support and strain relief
- Smooth funnel entry provides easy wire insertion
- Transparent heat shrink insulation provides waterproofing and weather resistance

Application

For Splicing Aircraft And Commercial Flexible Cables

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor Range	#14 AWG to #16 AWG

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	38 mm
Package Height	0.000 in
Dimension - Inside Diameter	0.2 in
inch	
Dimension - Strip Length inch	11/32 in
Dimension - Length Overall	1.50 in
inch	

General

Sub Brand	HYDENT
Insulation Type	Heat Shrink
Trade Name	HYDENT™
Plated	Y
Insulation	Y
Type	YSE-H, Heat Shrink
UPC 14 Digit GTIN	00781810525487
Material	Copper
Plating Type	Tin
UPC	781810525487

Logistics

Minimum Pack Quantity	100
Carton Quantity	100
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)