



YSHG4429 Compression H-Tap Connector

By Burndy
Catalog # [YSHG4429](#)

Copper Compression Double H- Tap Connector, 2 AWG - 250 kcmil (Tap), #8 & #9 Rebar/ 1" Ground Rod

Features

- UL467 Listed
- Suitable for direct burial in earth or concrete
- High conductivity copper extrusion minimizes resistance and eliminates corrosion due to dissimilar metals
- Grooves are prefilled with PENETROX™ E2 oxide inhibitor and individually sealed inhibiting moisture and contaminants

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 467, Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rebar Run Range	8 -9
Conductor - Rebar Run	• 8 • 9
Conductor - Rod Run Range	1 in
Conductor - Rod Run	1 in
Conductor - Copper Str Tap Range	2 AWG-250 kcmil
Conductor - Copper Str Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG

- 4/0 AWG
- 250 kcmil

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width mm	82 mm
Dimension - Width inch	3.22 in
Dimension - Length Overall inch	2.44 in

General

Trade Name	HYGROUND®
Die Index	KR
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810128657
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810128657
UPC 14 Digit GTIN	00781810128657

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)