

YSM2C, Uninsulated Parallel Splice For 42,613 - 66,832 cmils

By Burndy
Catalog # [YSM2C](#)

Uninsulated Parallel Splice For 42,613 - 66,832 cmils, Seamless Tubing, Beveled Barrel, Tin Plated



Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 12 AWG • 10 AWG
Conductor Size	42,613 - 66,832 cmils
Conductor - Copper Solid Size	• 12 AWG • 11 AWG • 10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	12 AWG-10 AWG

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Strip Length inch	11/16
Dimension - Length Overall inch	0.62 in

General

Product Family	COMPRESSION
Trade Name	HYLINK™
Die Index	10
Feature - Barrel Style	Chamfered
Plated	Yes
Color Code	Brown
Sub Brand	HYLINK
Product Type	Splice
UPC	781810805763
Type	YSM
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810805763
UPC 14 Digit GTIN	00781810805763

Logistics

Minimum Pack Quantity	1
Pallet Quantity	99999
Carton Quantity	200

Operational

Temperature Rating	90
--------------------	----

Product Assets

[Catalog \[English\]](#)